

Открываем вкладку File далее Print.

Прописываем настройки вручную.

Пример составлен по формату А4.

Printer: Linotronic 930

Print Style: Custom Settings

Copies: 1

 Collate


Pages: All

 Spreads

Sequence: All

 Back to Front

Scale: 100%

 Fit in Print Area

- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed
- Layers
- Transparency
- OPI
- JDF
- Advanced
- Summary

Device Options

PPD: Linotronic 930 V 3.0

Size: Custom

Width: 230 mm

Page Gap: 0 mm

Height: Auto

Paper Offset: 0 mm

Position: Center Horizontal

Resolution: 2438 dpi

 Negative Print PostScript Error Handler

Properties...

Print

Cancel

Capture Settings

Printer: Linotronic 930

Print Style: Custom Settings

Copies: 1

 Collate


Pages: All

 Spreads

Sequence: All

 Back to Front

Scale: 100%

 Fit in Print Area

- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed
- Layers
- Transparency
- OPI
- JDF
- Advanced
- Summary

Page Options

Orientation: Portrait Landscape Include Blank Pages Thumbnails

Page Flip: None

Page Tiling: Off

Overlap: Absolute Overlap

Properties...

Print

Cancel

Capture Settings



Printer: Linotronic 930


Print Style: Custom Settings

Copies: 1 Collate

Pages: All Spreads

Sequence: All Back to Front

Scale: 100% Fit in Print Area



- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed
- Layers
- Transparency
- OPI
- JDF
- Advanced
- Summary

Color Options

Mode: Composite

Setup: Composite CMYK

Halftones: Conventional Frequency: 60

	Plate	Halftone	Frequency	Angle	Function
<input checked="" type="checkbox"/>	Cyan	-	60	105°	Default
<input checked="" type="checkbox"/>	Magenta	-	60	75°	Default
<input checked="" type="checkbox"/>	Yellow	-	60	90°	Default
<input checked="" type="checkbox"/>	Black	-	60	45°	Default

Properties...

Print

Cancel

Capture Settings

Printer: Linotronic 930

Print Style: Custom Settings

Copies: 1

 Collate


Pages: All

 Spreads

Sequence: All

 Back to Front

Scale: 100%

 Fit in Print Area

- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed
- Layers
- Transparency
- OPI
- JDF
- Advanced
- Summary

Picture Options

Output: Normal

Data: Binary

 Overprint EPS/PDF Black Full Resolution TIFF Output

Properties...

Print

Cancel

Capture Settings

Printer: Linotronic 930

Print Style: Custom Settings

Copies: 1

 Collate


Pages: All

 Spreads

Sequence: All

 Back to Front

Scale: 100%

 Fit in Print Area

- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed
- Layers
- Transparency
- OPI
- JDF
- Advanced
- Summary

Font Options

 Select All Optimize Font Forma

Download	Font
<input checked="" type="checkbox"/>	Arial
<input type="checkbox"/>	
<input type="checkbox"/>	
<input type="checkbox"/>	

Properties...

Print

Cancel

Capture Settings

Printer: Linotronic 930

Print Style: Custom Settings

Copies: 1

 Collate


Pages: All

 Spreads

Sequence: All

 Back to Front

Scale: 100%

 Fit in Print Area

- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed
- Layers
- Transparency
- OPI
- JDF
- Advanced
- Summary

Registration Marks Options

Mode: Centered

Width: 0,088 mm

Length: 4,939 mm

Offset: 3,175 mm

 Include Bleed Marks

Properties...

Print

Cancel

Capture Settings

Printer: Linotronic 930

Print Style: Custom Settings

Copies: 1

 Collate


Pages: All

 Spreads

Sequence: All

 Back to Front

Scale: 100%

 Fit in Print Area

- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed**
- Layers
- Transparency
- OPI
- JDF
- Advanced
- Summary

Bleed Options

Bleed Type: Symmetric

Amount: 5 mm

Left: 0 mm

Bottom: 0 mm

Right: 0 mm

 Clip at Bleed Edge

Properties...

Print

Cancel

Capture Settings



Printer:


Print Style:

Copies: Collate

Pages: Spreads

Sequence: Back to Front

Scale: Fit in Print Area



- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed
- Layers
- Transparency
- OPI
- JDF
- Advanced
- Summary

Layer Options

Select All Apply to Layout

Print		Name
<input checked="" type="checkbox"/>		Default

Plates used on Selected Layer

No selection

Properties...

Print

Cancel

Capture Settings

Printer: Linotronic 930

Print Style: Custom Settings

Copies: 1

 Collate


Pages: All

 Spreads

Sequence: All

 Back to Front

Scale: 100%

 Fit in Print Area

- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed
- Layers
- Transparency
- OPI
- JDF
- Advanced
- Summary

Transparency Rendering Options

Item	Resolution	
Vector Images	300	↕ dpi
Blends	150	↕ dpi
Drop Shadows	150	↕ dpi

 Upsample Rotations

To 300 dpi for images less than 200 dpi

 Ignore Transparency Flattening

Properties...

Print

Cancel

Capture Settings

Printer: Linotronic 930

Print Style: Custom Settings

Copies: 1

 Collate


Pages: All

 Spreads

Sequence: All

 Back to Front

Scale: 100%

 Fit in Print Area

- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed
- Layers
- Transparency
- OPI**
- JDF
- Advanced
- Summary

OPI Options

 OPI Active

TIFF Options

 Include Images Low Resolution

EPS Options

 Include Images

Properties...

Print

Cancel

Capture Settings

Printer: Linotronic 930

Print Style: Custom Settings

Copies: 1

 Collate


Pages: All

 Spreads

Sequence: All

 Back to Front

Scale: 100%

 Fit in Print Area

- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed
- Layers
- Transparency
- OPI
- JDF
- Advanced
- Summary

JDF Options

 Output JDF

Include Job Jacket Contact: None

Properties...

Print

Cancel

Capture Settings

Printer: Linotronic 930

Print Style: Custom Settings

Copies: 1

 Collate


Pages: All

 Spreads

Sequence: All

 Back to Front

Scale: 100%

 Fit in Print Area

- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed
- Layers
- Transparency
- OPI
- JDF
- Advanced
- Summary

Advanced Options

PostScript Level: PostScript Level 3

Properties...

Print

Cancel

Capture Settings

Printer: Linotronic 930

Print Style: Custom Settings

Copies: 1

 Collate


Pages: All

 Spreads

Sequence: All

 Back to Front

Scale: 100%

 Fit in Print Area

- Device
- Pages
- Color
- Pictures
- Fonts
- Marks
- Bleed
- Layers
- Transparency
- OPI
- JDF
- Advanced
- Summary

Summary

General

Imageable Area

W: 230 mm

H: 313,267 mm

Layout Size

W: 210 mm

H: 297 mm

Device

Printer Description: Linotronic 930 V 3.0

Page Size:

W: 230 mm

H: Auto

Page Gap: 0 mm

Paper Offset: 0 mm

Properties...

Print

Cancel

Capture Settings